

メッシュ	線径φ (mm)	オープニング (mm)	空間率 (%)	メッシュ	線径φ (mm)	オープニング (mm)	空間率 (%)	メッシュ	線径φ (mm)	オープニング (mm)	空間率 (%)	メッシュ	線径φ (mm)	オープニング (mm)	空間率 (%)	メッシュ	線径φ (mm)	オープニング (mm)	空間率 (%)
1.5	1.90	15.03	78.8	5.0	0.83	4.35	70.0	10	0.80	1.74	46.9	18	0.43	0.98	48.3	70	0.12	0.24	44.8
	1.60	15.33	81.9		0.80	4.28	71.1		0.75	1.79	49.7		0.40	1.01	51.3		80	綾 0.18	0.14
2.0	1.90	10.80	72.3		0.75	4.33	72.7		0.70	1.84	52.5		0.37	1.04	54.4	100		綾 0.12	0.18
	1.60	11.10	76.4		0.70	4.38	74.3		0.65	1.89	55.4		0.34	1.07	57.6		綾 0.12	0.20	38.7
2.5	1.50	11.20	77.8	5.5	1.50	3.12	45.6	12	0.57	1.97	60.2	20	0.29	1.12	63.1	120	綾 0.10	0.13	27.8
	1.90	8.26	66.1		1.10	3.52	57.5		0.53	2.01	62.4		0.25	1.16	67.7		130	綾 0.10	0.15
	1.60	8.56	71.1	6.0	1.60	2.63	38.7		0.50	2.04	64.5		0.47	2.07	66.4	150		綾 0.090	0.122
	1.50	8.66	72.7		1.50	2.73	41.7		0.47	2.07	66.4		0.50	0.77	36.7		綾 0.080	0.132	38.7
3.0	1.20	8.96	77.8	6.5	1.20	3.03	51.3	14	0.45	2.09	67.7	24	0.47	0.80	39.7	165	綾 0.080	0.115	34.9
	1.10	9.06	79.5		1.10	3.13	54.8		0.43	2.11	69.0		0.45	0.82	41.7		180	綾 0.065	0.104
	1.00	9.16	81.4	7.0	1.00	3.23	58.4		1.00	1.12	27.9		0.43	0.84	43.7	200		綾 0.060	0.109
	1.90	6.57	60.2		0.95	3.28	60.2		0.95	1.17	30.4		0.40	0.87	46.9		220	綾 0.050	0.077
	1.60	6.87	65.8	0.90	3.33	62.0	0.90		1.21	33.1	0.37		0.90	50.2	230	綾 0.045		0.109	50.1
	1.50	6.97	67.7	0.80	3.43	65.8	0.80		1.32	38.8	0.34		0.93	53.6		250	綾 0.050	0.091	41.7
1.20	7.27	73.6	0.75	3.48	67.7	0.75	1.37	41.7	0.29	0.98	59.6	270	綾 0.045	0.096	46.4				
1.10	7.37	75.3	0.70	3.53	69.7	0.70	1.42	44.9	0.25	1.02	64.5		300	綾 0.045	0.096	46.4			
1.00	7.47	77.8	0.65	3.58	71.6	0.65	1.47	48.0	0.22	1.05	68.4	325		綾 0.053	0.074	34.0			
3.2	1.90	6.04	57.9	7.5	1.10	2.81	51.6	16	0.57	1.55	53.4		28	0.40	0.66	38.8	250	綾 0.050	0.077
	1.50	6.44	65.8		0.95	2.96	57.3		0.50	1.62	58.4	0.37		0.69	42.3	270		綾 0.050	0.077
	1.10	6.84	74.2	0.90	3.01	59.2	0.47		1.65	60.5	0.34	0.72		46.1	300		綾 0.040	0.070	40.7
	1.00	6.94	76.4	0.80	3.11	63.2	0.45		1.67	62.1	0.29	0.77		52.7		325	綾 0.040	0.070	40.7
3.5	0.95	6.99	77.5	8.0	0.75	3.16	65.3	18	0.80	1.01	31.1	30	0.25	0.81	58.4		350	綾 0.040	0.061
	1.90	5.36	54.5		0.70	3.21	67.4		0.75	1.06	34.4		0.29	0.61	46.4	375		綾 0.035	0.067
	1.60	5.66	60.8	0.65	3.26	69.5	0.70		1.11	37.6	0.34		0.51	35.8	400		綾 0.030	0.072	49.8
	1.50	5.76	62.4	0.57	3.34	73.0	0.65		1.16	41.2	0.29		0.56	43.4		425	綾 0.030	0.072	49.8
1.20	6.06	69.7	8.5	1.10	2.53	48.6	0.57	1.24	47.0	0.25	0.59	49.8	450	綾 0.040	0.054		33.0		
1.10	6.16	72.0		0.80	2.83	60.8	0.50	1.31	52.4	0.22	0.64	54.9		475	綾 0.030	0.054	41.9		
1.00	6.26	74.3	0.75	2.88	62.9	0.47	1.34	54.9	0.29	0.50	40.1	500	綾 0.030		0.054	41.9			
4	1.90	4.45	49.1	9.0	0.65	2.98	67.4	20	0.45	1.36	56.4		32	0.25	0.54	46.8	525	綾 0.030	0.054
	1.60	4.75	56.0		0.57	3.05	71.1		0.43	1.38	58.2	0.25		0.47	38.8	550		綾 0.030	0.054
	1.50	4.85	58.3	9.5	1.20	1.98	38.8		0.40	1.41	60.7	綾 0.29		0.35	29.9		575	綾 0.026	0.037
	1.20	5.15	65.8		1.10	2.08	42.7		0.37	1.44	63.4	0.25		0.39	35.3	600		綾 0.025	0.025
	1.10	5.25	67.9	1.00	2.18	47.1	0.34		1.47	66.0	0.22	0.42		42.7	625		綾 0.020	0.020	25.0
	1.00	5.35	71.1	0.95	2.23	49.1	0.29		1.52	70.6	0.18	0.46		51.7		650	綾 0.020	0.020	25.0
	0.95	5.40	72.3	10.0	0.90	2.28	51.3		0.70	0.89	31.4	0.16		0.48	56.0		675	綾 0.020	0.020
	0.90	5.45	73.7		0.80	2.38	56.0		0.65	0.94	34.9	0.14		0.49	60.8	700		綾 0.020	0.020
	0.83	5.52	75.6	10.5	0.75	2.43	58.3		0.57	1.02	41.1	0.14		0.46	59.1		725	綾 0.020	0.020
	0.80	5.55	76.4		0.70	2.48	60.8		0.50	1.09	47.1	綾 0.23		0.28	29.9	750		綾 0.020	0.020
4.2	1.00	5.05	69.7	0.65	2.53	63.2	0.47	1.12	49.6	0.21	0.30	34.6	775	綾 0.020	0.020		25.0		
	1.50	4.14	53.9	0.57	2.61	67.3	0.45	1.14	51.4	0.18	0.33	41.9		800	綾 0.020	0.020	25.0		
4.5	1.10	4.54	64.8	11.0	0.50	2.68	71.1	0.43	1.16	53.2	0.16	0.34	46.9		825	綾 0.020	0.020	25.0	
	1.90	3.18	39.2		0.47	2.71	72.6	0.40	1.19	56.0	0.15	0.35	49.7	850		綾 0.020	0.020	25.0	
5.0	1.60	3.48	46.9	11.5	0.45	2.73	73.7	0.37	1.22	58.8	0.14	0.37	52.5		875	綾 0.020	0.020	25.0	
	1.50	3.58	49.7		0.80	2.02	51.3	0.34	1.25	61.8	綾 0.23	0.19	20.9	900		綾 0.020	0.020	25.0	
	1.20	3.88	58.4	0.65	2.17	59.2	0.29	1.30	66.9	0.19	0.23	30.0	925		綾 0.020	0.020	25.0		
	1.10	3.98	61.4	12.0	1.10	1.44	32.1	0.57	0.84	35.5	0.18	0.24		32.6	950	綾 0.020	0.020	25.0	
	1.00	4.08	64.5		1.00	1.54	36.7	0.50	0.91	41.6	0.16	0.26	38.7	975		綾 0.020	0.020	25.0	
	0.95	4.13	66.1	12.5	0.95	1.59	39.2	0.47	0.94	44.5	0.15	0.27	41.7		1000	綾 0.020	0.020	25.0	
0.90	4.18	67.7	0.90		1.64	41.7	0.45	0.96	46.4	0.14	0.28	44.8	1025	綾 0.020		0.020	25.0		

※ 綾 = 綾織

メッシュ : インチ間の糸の本数  
 線径 : 糸の大きさ  
 オープニング : 糸と糸の間の距離 (空間)  
 空間率 : メッシュフィルターの空間率 (オープニングエリア)



弊社HPも、ご参照ください